

## Product information

### Dosage Module - Dosage module



#### Description

The dosage module for the mzs-2505 (S/F), mzs-2905 (S/F) and mzs-4605 (S/F) pumps can be used for volumetric dosage of adhesives like UV cure adhesive, epoxy resin, screw fixing varnish, lubricants and silicon. The dosage module suits the dispensing of smallest amounts of liquids requiring highly precise handling (small beads or spots) and the absence of afterrun. The liquid can be supplied from a 30 or 55 ml disposable cartridge which is directly connected to the pump. For liquids with higher viscosity, pressure of up to 5 bar may be applied to the cartridge. An air discharge screw enables to bleed the system after cartridge exchange or to supply flushing liquid for cleaning. The dosing needles can be directly connected to the Luer-Lock male adapter of the pump. With the fixing bracket the module may be mounted onto the handling device.

#### Advantages

- High dosage precision  
precision CV <1% at low volumes
- Exchangeable reservoir  
for cartridges 30 and 55 ml
- Constant precision  
pump parts made of tungsten carbide
- Broad viscosity range  
adhesives, oil, grease, polymers, gel
- Compact dimensions  
120 x 60 x 200 mm (S/F-version: 117 x 69 x 237 mm),  
including controller and cartridge
- Precision motor and sophisticated control  
DC-servomotor with integrated microcontroller
- Dosage of small amounts  
discrete dosage and continuous delivery

#### Applications

- Bead dispense
- Filling technology
- Assembly stations
- Backfill of electronic components
- Labeling
- Oil dispensing
- Adhesive dispensing
- Grease dispensing
- Silicon dispensing

## Technical data

Smallest dosage volume	0.25 - 2 *µl
Differential pressure range	0 - 50 bar (725 psi) *
Initial pneumatic pressure	0 - 5 bar (73 psi)
Viscosity range	up to 50,000 *mPas
Precision CV	< 1 %% (Coefficient of variation CV)
Dosing needle connection	Luer-Lock male
Cartridge connection	Luer-Lock female
Wetted parts	stainless steel 316L, Ni-based tungsten carbide, shaft seal: graphite-reinforced PTFE, PEEK, 316L; static seals: FPM, optional: FFPM, EPDM
Motor	DC-servomotor, 24 V DC, 44 W
Interface	0–10 V, RS-232, 1 digital input/output
Controller	integrated 16-bit microcontroller with 7936 Bytes program memory for dosage tasks
Dimensions (L x W x H)	120 x 64 x 230 mm (S/F-version: 117 x 69 x 237 mm)
Weight	approx. 1,200 g
Remarks	* depending on the size of the micro ring gear pump.

### Notice

Even if single parameters are within the indicated performance range of technical data, certain parameter combinations may not be achievable. Single parameters may exceed their indicated performance range under adequate circumstances. For detailed evaluation please contact HNP Mikrosysteme. Actual performance may vary. Specifications are subject to change without notice.

## Accessories

- m zr-2505
- m zr-4605
- m zr-2905

## Patents and trademarks

Micro annular gear pumps (and housings) are protected by assigned patents: EP 1 354 135 B1; US 7,698,818 B2; DE 10 2011 001 041 B4; CN 103 348 141 B; US 10,012,220 B2; CN 103 732 921 B; US 9,404,492 B2; US 6,520,757 B1.

HNP M<sup>®</sup>, m zr<sup>®</sup>, MoDoS<sup>®</sup>, µ-Clamp<sup>®</sup>, µDispense<sup>®</sup>, Centifluidic Technologies<sup>®</sup> are registered German trademarks of HNP Mikrosysteme GmbH.

## Contact

HNP Mikrosysteme GmbH  
Bleicherufer 25  
19053 Schwerin  
Germany

T +49 385 52190-300  
F +49 385 52190-333  
info@hnp-mikrosysteme.de

Last update 2019/07