

Filter-pump functional module F-P

Functional module for micro annular gear pumps of low pressure series and modular series



similar image

- **Low void volume**
integration of micro annular gear pump and filter, short internal fluid connections
- **Compact dimensions, low weight**
39 x 25 x 38.5 mm, approx. 255 g (resp. without pump)
- **Flexible use for mzr®-pumps of low pressure and modular series**
mzr-2521, mzr-2921 or mzr-2542, mzr-2942, resp.
- **Wide range of volume flows**
volume flows 0.15 – 9 ml/min resp. 0.3 – 18 ml/min
- **Safety of operation through wire mesh filter**
protection of pump and downstream fluidic structures from contaminations
- **Easy replacement of pump and filter**
mounting of pump via stainless steel sheet, one-piece screw-in filter

The filter-pump functional module F-P allows the combination of micro annular gear pump and filter with short direct connections. The void volume of this compact system is low and the expenses of connecting elements are obsolete. The integrated wire mesh filter with a mesh size of 10 µm

preventatively protects the pump as well as the downstream fluidic micro structures from contamination. Replacement of the easy accessible filter is uncomplicated, removing of the pump is unnecessary. The functional module can be used flexibly for several sizes of pumps of the low pressure and

modular pump series. The modules can ideally be used for precise and reliable discrete and continuous dosing of volume flows from 0.15 to 18 ml/min for applications in the field of analytical instrumentation, medical engineering and micro reaction technology as well as other areas.

Application fields

- Analytical instrumentation
- Laboratory automation
- Diagnostics
- Biotechnology
- Micro reaction technology
- Research and Development

Even if single parameters are within the indicated performance range of technical data, certain parameter combinations may not be achievable. Single parameters may exceed their indicated performance range under adequate circumstances. For detailed evaluation please contact HNP Mikrosysteme. Actual performance may vary. Specifications are subject to change without notice.

Technical data

Flow rate	0.15 – 9 ml/min resp. 0.3 – 18 ml/min *
Differential pressure range	0 – 1.5 bar (22 psi) resp. 0 – 3 bar (44 psi) *
Max. inlet pressure	1 bar (15 psi)
Liquid temperature range	-20 ... +60 °C (-4 ... +140 °F)
Viscosity range	0.3 – 100 mPas
Void volumes	Fluid channels 30 µl, filter volume 1.6 ml
Fluid connection	1/4" -28 UNF
Mounting parts	2x Ø3.4 mm, 2x M3x7
Filter	mesh wire filter with screw thread mesh size 10 µm, filter area 6 cm ²
Wetted parts	filter: stainless steel 316L, epoxy resin; static seals: FPM, optional: FFPM manifold adapter: stainless steel 316L
Dimensions (L x W x H)	39 x 25 x 38.5 mm (without pump)
Weight	ca. 255 g (without pump)

* depending on pump

Contact

HNP Mikrosysteme GmbH
Bleicherufer 25 · D-19053 Schwerin

phone +49 385 52190-301
fax +49 385 52190-333

e-mail info@hnp-mikrosysteme.de
<http://www.hnp-mikrosysteme.de>

